



Digital caliper SET TESA-CAL IP67, measurement range 150 mm, Number of digital calipers: 10



Order data

Order number	405522 10
GTIN	4067263132752
Item class	45A

Description

Version:

- Perfect guidance of the slide on the rail for easy and even smooth running.
- Sturdy design for long life and long-term stability of results.
- High protection category against dust and liquids.
- Easy to read with large, sharp-contrast round scale.
- Long battery life avoids frequent changing of batteries.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

External, internal, step and depth measurements.

Supplied with:

1 battery No. 081560 size CR2032. Set consisting of 10x No. 412760 size 150.

Technical description

Article no of the battery / rechargeable battery fitted	081560 CR2032
Depth gauge	rectangular 3.7×1.3
Reversible reading	mm / inch
Number of batteries contained	1

Scale divisions	0.01 mm
Power supply	Battery-powered
Scale divisions	0.0005 in
Standard	ISO 13385
Measuring range	0 - 150 mm
Measurement value and zero point preserved after reactivation from standby	yes
Jaw length	40 mm
Calibration	A1
Working time	12000 hours
Auto switch-off	yes
Measurement deviation E MPE	±0.03 mm
Measured value saving	Once-off setting of the zero position
Depth gauge available	yes
IP Index of Protection	IP 67
Digit height LCD display	11 mm
Automatic stand-by circuit.	yes
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 10X200 mm	021010 10X200
Calibration Calipers / depth gauges maximum measuring range 10X200 mm	021000 10X200

Accessories

Button cell / special battery Battery type CR2032

081560 CR2032