

Mitutoyo
Digital caliper SET IP67, measurement range 150 mm, Number of digital calipers: 10

Order data

Order number	412629 10
GTIN	4067263132813
Item class	44A

Description
Version:

Electronic caliper with absolute electronics and large easy-to-read display. Resistant to water, oil, and dust. Low energy consumption permits 18000 h continuous use on a single battery (size 300: 5000 h). The device is turned on automatically when it is moved and switches off automatically when not used for about 20 minutes.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357.

3 x digital calipers No. 412623 size 150. Set consisting of 10x No. 412623 size 150.

Technical description

Depth gauge	rectangular 3.7×1.4
Measuring range	0 - 150 mm
Auto switch-off	yes
Working time	15000 h
Depth gauge available	yes

Scale divisions	0.01 mm
Jaw length	40 mm
Article no of the battery / rechargeable battery fitted	081560 357
Measurement deviation E MPE	± 0.02 mm
Measured value saving	Once-off setting of the zero position
Power supply	Battery-powered
Calibration	A1
IP Index of Protection	IP 67
Number of batteries contained	1
Standard	ISO 13385
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 10X200 mm	021010 10X200
Calibration Calipers / depth gauges maximum measuring range 10X200 mm	021000 10X200

Accessories

Depth gauge holder, metal with 2 screws	412120
Button cell / special battery Battery type 357	081560 357