

**Mitutoyo**
**Digital caliper SET with AOS system, measurement range 150 mm, Number of digital calipers: 3**


## Order data

Order number	412633 3
GTIN	4067263132868
Item class	44A

## Description

### Version:

Measured result is displayed in easy-to-read characters (height 9 mm). The **AOS (Advanced Onsite Sensor)** electromagnetic measurement system offers enhanced protection against water and dust.

- **Absolute scale, no zeroing necessary, resulting in faster, more reliable measuring.**
- **Low current consumption (20000 hours continuous use), battery charge indicator.**

### Supplied with:

**3 × digital calipers** No. 412632 size 150. Set consisting of 3× No. 412632 size 150.

### Optional extras:

Battery compartment cover No. 412239 size B.

## Technical description

Calibration	A1
Standard	ISO 13385
Power supply	Battery-powered
Depth gauge available	yes
Digit height LCD display	9 mm
Measuring range	0 - 150 mm
Depth gauge	rectangular 3.7×1.4
Number of batteries contained	1

Measurement deviation E MPE	± 0.02 mm
Scale divisions	0.01 mm
Working time	20000 h
Jaw length	40 mm
Article no of the battery / rechargeable battery fitted	081560 357
Measurement method of the measuring instrument	electro-magnetic inductive procedure
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 3X200 mm	021000 3X200
DAkkS calibrationCalipers / depth gauges maximum measuring range 3X200 mm	021010 3X200

## Accessories

Battery compartment cover Type B	412239 B
Depth gauge holder, metal with 2 screws	412120
Button cell / special battery Battery type 357	081560 357