

Mahr**Digital caliper SET with large display and rod type depth gauge,
measurement range 150 mm, Number of digital calipers: 3****Order data**

Order number	412718 3
GTIN	4067263132882
Item class	43A

Description**Version:**

Easy-to-read, high-contrast LCD display with 11 mm high characters. Modern energy-efficient measuring system, operational life approx. 3 years. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped. With rod type depth gauge.

Supplied with:

1 battery No. 081560 size CR2032. Set consisting of 3× No. 412716 size 150.

Technical description

Measurement deviation E MPE	±0.03 mm
Measuring range	0 - 150 mm
Depth gauge	∅ 1.6
Power supply	Battery-powered
Jaw length	40 mm
Scale divisions	0.0005 in

Reversible reading	mm / inch
Standard	ISO 13385
Number of batteries contained	1
Depth gauge available	yes
Measured value saving	MAHR reference-lock system
Scale divisions	0.01 mm
Digit height LCD display	11 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Working time	approx. 3 years
Calibration	A1
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 3X200 mm	021010 3X200
Calibration Calipers / depth gauges maximum measuring range 3X200 mm	021000 3X200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------