



Digital caliper SET IP67 with rod type depth gauge, measurement range 150 mm, Number of digital calipers: 3



Order data

Order number	412735 3
GTIN	4067263132912
Item class	43A

Description

Version:

Clearly legible, high-contrast LCD display. Waterproof inductive measurement system with reference-lock function. The measuring faces are precision lapped.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

3 x digital calipers No. 412731 size 150.

1 battery No. 081560 size CR2032. Set consisting of 3x No. 412731 size 150.

Technical description

Measurement deviation E MPE	± 0.03 mm
Power supply	Battery-powered
Measured value saving	MAHR reference-lock system
Calibration	A1
Scale divisions	0.0005 in
IP Index of Protection	IP 67

Scale divisions	0.01 mm
Depth gauge available	yes
Article no of the battery / rechargeable battery fitted	081560 CR2032
Reversible reading	mm / inch
Jaw length	40 mm
Depth gauge	Ø 1.6
Number of batteries contained	1
Standard	ISO 13385
Measuring range	0 - 150 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 3X200 mm	021000 3X200
DAkkS calibrationCalipers / depth gauges maximum measuring range 3X200 mm	021010 3X200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------