

 Mahr

Digital caliper SET IP67 with rod type depth gauge, measurement range 150 mm, Number of digital calipers: 10



Order data

Order number	412735 10
GTIN	4067263132899
Item class	43A

Description

Version:

Clearly legible, high-contrast LCD display. Waterproof inductive measurement system with reference-lock function. The measuring faces are precision lapped.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

3 × digital calipers No. 412731 size 150.

1 battery No. 081560 size CR2032. Set consisting of 10× No. 412731 size 150.

Technical description

Standard	ISO 13385
Jaw length	40 mm
Measurement deviation E MPE	±0.03 mm
Reversible reading	mm / inch
Measuring range	0 - 150 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032

Scale divisions	0.0005 in
Calibration	A1
Power supply	Battery-powered
Measured value saving	MAHR reference-lock system
Number of batteries contained	1
Depth gauge	Ø 1.6
Depth gauge available	yes
IP Index of Protection	IP 67
Scale divisions	0.01 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 10X200 mm	021000 10X200
DAkkS calibrationCalipers / depth gauges maximum measuring range 10X200 mm	021010 10X200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------