



## Digital caliper SET with large display and rod type depth gauge, measurement range 150 mm, Number of digital calipers: 10



### Order data

Order number	412718 10
GTIN	4067263132875
Item class	43A

### Description

#### Version:

Easy-to-read, high-contrast LCD display with 11 mm high characters. Modern energy-efficient measuring system, operational life approx. 3 years. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped. With rod type depth gauge.

#### Supplied with:

1 battery No. 081560 size CR2032. Set consisting of 10× No. 412716 size 150.

### Technical description

Calibration	A1
Scale divisions	0.0005 in
Measured value saving	MAHR reference-lock system
Measurement deviation E MPE	±0.03 mm
Scale divisions	0.01 mm
Digit height LCD display	11 mm
Jaw length	40 mm

Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Reversible reading	mm / inch
Measuring range	0 - 150 mm
Working time	approx. 3 years
Depth gauge available	yes
Number of batteries contained	1
Depth gauge	Ø 1.6
Standard	ISO 13385
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 10X200 mm	021000 10X200
DAkkS calibrationCalipers / depth gauges maximum measuring range 10X200 mm	021010 10X200

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------