

**Cordless angle grinder GWS, Type: 18V-180P****Order data**

Order number	077120 18V-180P
GTIN	4053423246209
Item class	03C

Description**Version:****Small and light 180 mm 18 V cordless angle grinder:**

- Thanks to the 180 mm grinding disc and small gearbox head, it offers the same cutting depth as a large 230 mm angle grinder, but is up to 35% lighter.
- Biturbo Brushless technology for fast cutting into a wide range of materials.
- PROtection switch, KickBack Control, intelligent braking system.

Supplied with:

Including safety guard, additional handle, cutting discs, L-BOXX. Without battery and charger.

Note:

See No. 073854 and No. 073866 for suitable spare batteries and chargers.

Technical description

Manufacturer's designation	GWS 18V-180P
Type of rechargeable battery	Lithium-ion
maximum disc \varnothing	180 mm
maximum cutting depth	61 mm
Battery voltage	18 V

Packaging	Modular case (L-Boxx)
Weight	2.8 kg
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum vibration to EN	4.1 m/s ²
Number of rechargeable batteries contained	0
Power supply	Mains operated
Special features	Dead man's switch
maximum speed	6100 min ⁻¹
Restart block	yes
Type of product	Angle grinder