



## Digital caliper SET TWIN-CAL IP67 with rod type depth gauge, measurement range 150 mm, Number of digital calipers: 3



### Order data

|              |               |
|--------------|---------------|
| Order number | 405521 3      |
| GTIN         | 4067263132745 |
| Item class   | 45A           |

### Description

#### Version:

- Perfect guidance of the slide on the rail for easy and even smooth running.
- Sturdy design for long life and long-term stability of results.
- High protection category against dust and liquids.
- Easy to read with large, sharp-contrast round scale.
- Long battery life avoids frequent changing of batteries.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Application:

External, internal, step and depth measurements.

#### Supplied with:

1 battery No. 081560 size CR2032. Set consisting of 3x No. 412785 size 150.

#### Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

### Technical description

|                    |           |
|--------------------|-----------|
| Standard           | ISO 13385 |
| International size | CR2032    |

|   |                                       |
|---|---------------------------------------|
| Depth gauge   | Ø 1.6                                 |
| Automatic stand-by circuit.                             | yes                                   |
| Number of batteries contained                           | 1                                     |
| Measurement deviation E MPE                             | ±0.03 mm                              |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032                         |
| Auto switch-off   | yes                                   |
| IP Index of Protection                                  | IP 67                                 |
| Calibration   | A1                                    |
| Power supply  | Battery-powered                       |
| Reversible reading                                      | mm / inch                             |
| Working time  | 12000 h                               |
| Jaw length  | 40 mm                                 |
| Depth gauge available                                   | yes                                   |
| Battery type  | Button cell                           |
| Measuring range   | 0 - 150 mm                            |
| Scale divisions   | 0.0005 in                             |
| Measured value saving                                   | Once-off setting of the zero position |
| Digit height LCD display                                | 11 mm                                 |
| Scale divisions   | 0.01 mm                               |
| Interface   | TESA Link Connector TLC               |
| Interface   | TESA Link Connector TLC               |
| Interface   | USB interface                         |
| Interface   | USB interface                         |
| Measurement technology                                  | digital                               |
| Material  | Stainless steel, INOX                 |
| all parts   | hardened                              |
| Packaging   | sturdy box                            |
| Type of product   | Universal calipers                    |

## Services

|   |              |
|---|--------------|
| CalibrationCalipers / depth gauges maximum measuring range 3X200 mm       | 021000 3X200 |
| DAkkS calibrationCalipers / depth gauges maximum measuring range 3X200 mm | 021010 3X200 |

---

## Accessories

|   |               |
|---|---------------|
| Data cable TLC, 2 m Type USB                      | 498918 USB    |
| Data cable TLC, 2 m Type D                        | 498918 D      |
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |