

HOLEX®
DCMT 11T302 Set 10 pieces, Grade: HBX130

Order data

Order number	260504 HBX130
GTIN	4045197670021
Item class	22D

Description

DCMT 11T302 Set of 10 pieces HBX130 Grade: HBX130

Chip breaker: MM

Cutting depth a_p : 0.1 - 3.75 mm

Feed f : 0.06 - 0.36 mm/rev.

Cutting speed v_c main application: 60 - 200 m/min

Technical description

Chip breaker	MM
Cutting depth a_p	0.1 - 3.75 mm
Cutting speed v_c main application	60 - 200 m/min
Corner radius	0.2 mm
Cutting conditions	slightly interrupted
Feed f	0.06 - 0.36 mm/rev.
Main application	M

Grade	HBX130
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DCMT 11T302
Number of changes/inserts	2
Type of product	Indexable insert for turning