

**Garant**
**Screw-on toolholder, left-hand, Shank / insert size: 20/10mm**

**Order data**

Order number	260607 20/10
GTIN	4045197655394
Item class	21T

**Technical description**

Shim screw	269013 2
Head length L <sub>1</sub>	17 mm
Insert size	10 mm
ISO code toolholder	SRGCR/L 2020K10
suitable indexable insert	RC.T 1003
Shim	269005 11
Pack of insert screws	269028 2
Functional width L <sub>4</sub>	25 mm
Shank size	20 mm
Overall length L	125 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	30 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Shim screw Type 2	269013 2
Shim Type 11	269005 11
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500