

**Garant****Modular floor mat, dark grey speckled, Type: D****Order data**

Order number	964460 D
GTIN	4067263137351
Item class	9GM

**Description****Version:**

Modular industrial workplace mat for medium to high loads, can be installed in a flexible interlocking system. The ergonomic rubber mat is suitable for dry and wet walking and standing workplaces. The mat surface has an optimally coordinated pivot point and very good slip resistance and position stability. Very easy-to-clean surface with light-reflecting properties. The oil-resistant floor mat has a fire protection class Bfl-s1. Due to the elastic properties of the rubber compound and the special geometry on the rear, the mat has a particularly shock-absorbing and activating effect and protects against unhealthy levels of coldness. Durable mat suitable for multi-shift operation. Electrically dissipative, surface resistance of less than  $10^7\Omega$ . The mat is marked with an ESD safety label. Bevelled edges on 3 sides to avoid the risk of stumbling. One side with puzzle-type teeth/dovetail connection. Start and end section for installation in rows.

**Standard:**

EN 61340-4-1, REACH-konform.

**Note:**

Can be installed on solid flooring such as concrete/screed, synthetic resin flooring, asphalt, tiles. The substructure must be level, clean and smooth. Rubber mats can easily be cut to size with the cutter tool.

**Technical description**

Fire protection class	Bfl-s1
Weight	18.3 kg
plug-in	yes

Hardness according to Shore A	55
Material	Nitrile rubber (NBR)
Width	100 cm
Thickness	16 mm
Length	132 cm
Design length	130 cm
Standing in comfort	Anti-fatiguing
Standing in comfort	Anti-slip
Standing in comfort	Insulation (temperature)
Shock protection	Floor
Material characteristics	oil-resistant
Material characteristics	flame resistant
Colour	dark grey speckled
Type of product	Workplace mat