



Boot, black/blue STEFANO XXSG BOA® black-blue Mid ESD, S3, EU shoe size: 41



Order data

Order number	092271 41
GTIN	4030839362785
Item class	09P

Description

Version:

STEFANO safety shoe from the ELTEN WELLMAXX product line.

- **Upper material of sturdy cowhide.**
- **Breathable textile lining.**
- **Closed, padded tongue.**
- **BOA® Fit closure system.**
- **Sole core of Infinergy® from BASF for shock absorption over the entire sole.**
- **Rough SAFETY-GRIP PU/PU sole.**
- **ARTISAN ESD insole.**
- **PU overcap to protect the uppers.**
- **Reflective strips for better visibility.**
- **ESD security.**

Standard:

EN ISO 20345:2011 S3 SRC

Inlay provision design type tested to DGUV regulations 191.

Technical description

Data sheet

Protection class	S3
Series	STEFANO
Gender	Gentlemen's
EU shoe size	41
Characteristics	Rotary closure
Puncture resistance	Textile
Colour	black/blue
Material of protective toe-cap	Steel
Standard	Inlay type-tested according to DGUV regulation 191
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Infinergy sole
Type of product	Safety boots

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/092271-41>
