

**ELTEN****Shoe, black/blue STEFANO XXSG BOA® black-blue Low ESD S3, EU shoe size: 48**

## Order data

Order number	092270 48
GTIN	
Item class	09P

## Description

### Version:

STEFANO safety shoe from the ELTEN WELLMAXX product line.

- **Upper material of sturdy cowhide.**
- **Breathable textile lining.**
- **Closed, padded tongue.**
- **BOA® Fit closure system.**
- **Sole core of Infinergy® from BASF for shock absorption over the entire sole.**
- **Rough SAFETY-GRIP PU/PU sole.**
- **ARTISAN ESD insole.**
- **PU overcap to protect the uppers.**
- **Reflective strips for better visibility.**
- **ESD security.**

### Standard:

EN ISO 20345:2011 S3 SRC

## Technical description

Protection class	S3
Puncture resistance	Textile

Standard	Inlay type-tested according to DGUV regulation 191
Gender	Gentlemen's
Material of protective toe-cap	Steel
Characteristics	Rotary closure
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Infinergy sole
Type of product	Safety boots