

**Garant**
**Screw-on toolholder, left-hand, Shank / insert size: 25/10mm**

**Order data**

Order number	260607 25/10
GTIN	4045197655400
Item class	21T

**Technical description**

Head length $L_1$	21 mm
Functional width $L_4$	32 mm
ISO code toolholder	SRGCR/L 2525M10
Shank size	25 mm
Pack of insert screws	269028 2
Shim	269005 11
suitable indexable insert	RC.T 1003
Insert size	10 mm
Shim screw	269013 2
Overall length L	150 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	30 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim screw Type 2	269013 2
Shim Type 11	269005 11
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500