

**Garant**
**Screw-on toolholder, right-hand, Shank / insert size: 20/12mm**

**Order data**

Order number	260706 20/12
GTIN	4045197653307
Item class	21T

**Technical description**

Head length L <sub>1</sub>	27 mm
Shim	269005 9
Shim screw	269013 5
Shank size	20 mm
Pack of insert screws	269028 20
ISO code toolholder	SSSCR/L 2020K12
suitable indexable insert	SC.. 1204..
Insert size	12 mm
Functional width L <sub>4</sub>	25 mm
Overall length L	125 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim screw Type 5	269013 5
Set of insert screws Type 20	269028 20
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 9	269005 9
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500