



Digital XTL bore gauge with Bluetooth, Measurement range: 20-25mm



Order data

Order number	428761 20-25
GTIN	2050002078017
Item class	46B

Description

Version:

3-point bore gauges for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

Supplied with:

Measuring lever, micrometer head with UKAS test certificate, 1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498950 (from size 20), No. 498951 (up to size 20), setting rings No. 484030, extensions No. 428510.

Technical description

Error limit	0.004 mm
Measuring range	20 - 25 mm

Data sheet

Number of batteries contained	1
Dimension a	0.5 mm
Scale divisions	0.001 mm
Standard measuring depth	66 mm
Power supply	Battery-powered
Article no of the battery / rechargeable battery fitted	081560 CR2032
Measuring depth with extension	216 mm
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 50 mm	022500 50

Accessories

Receiver / USB keyboard interface Type	498965
Multi-receiver / USB keyboard interface Type	498975
Setting ring DIN 2250 C Nominal size Ø 22 mm	484030 22
Setting ring DIN 2250 C Nominal size Ø 20 mm	484030 20
Connection cable Duplex Type USB2	498950 USB2

Connection cable Duplex Type 2	498950 2
Setting ringDIN 2250 C Nominal size Ø 24 mm	484030 24
Setting ringDIN 2250 C Nominal size Ø 25 mm	484030 25
Button cell / special battery Battery type CR2032	081560 CR2032
Extension for internal micrometers Type 4/150	428510 4/150
Setting ringDIN 2250 C Nominal size Ø 21 mm	484030 21
Setting ringDIN 2250 C Nominal size Ø 23 mm	484030 23