



Digital XTL bore gauge with Bluetooth, Measurement range: 16-20mm



Order data

Order number	428761 16-20
GTIN	2050002078024
Item class	46B

Description

Version:

3-point bore gauges for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

Supplied with:

Measuring lever, micrometer head with UKAS test certificate, 1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498950 (from size 20), No. 498951 (up to size 20), setting rings No. 484030, extensions No. 428510.

Technical description

Number of batteries contained	1
Standard measuring depth	62 mm

Data sheet

Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Measuring range	16 - 20 mm
Dimension a	0.5 mm
Power supply	Battery-powered
Error limit	0.004 mm
Measuring depth with extension	166 mm
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

Services

Calibration3-point internal micrometer maximum measuring range 20 mm	022500 20
DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Setting ringDIN 2250 C Nominal size Ø 17 mm	484030 17
Setting ringDIN 2250 C Nominal size Ø 16 mm	484030 16
Setting ringDIN 2250 C Nominal size Ø 18 mm	484030 18
Setting ringDIN 2250 C Nominal size Ø 19 mm	484030 19
Connection cable Duplex Type USB2	498951 USB2

Extension for internal micrometers Type 3/100	428510 3/100
Connection cable Duplex Type R2	498951 R2
Setting ringDIN 2250 C Nominal size Ø 20 mm	484030 20
Button cell / special battery Battery type CR2032	081560 CR2032