

**Pair of gloves 6845 // SKIN FLEX 3D, Glove size: 10****Order data**

| | |
|--------------|---------------|
| Order number | 094533 10 |
| GTIN | 4059904206779 |
| Item class | 09H |

Description**Version:**

SKIN FLEX 3D 6845. Very high cut protection (performance level F) and very comfortable to wear thanks to the 3D FIT fit. With reinforced thumb joint. Suitable for touch screens. Suitable for ESD workstations.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. Gloves which protect against electrostatic discharges do not insulate the hands against electrical voltages. Not suitable for working on live cables or for protection against electric shock - they protect only the product.

Technical description

| | |
|---------------------|----------------------|
| Protection category | Category II |
| Type of glove | Cut-resistant gloves |
| Contents | 1 |

| | |
|------------------------------|----------------------------|
| Glove characteristics | Suitable for touch screens |
| electrostatic characteristic | EGB/ESD |
| EN 388 | 4X42F |
| Backing material | Nylon |
| Coating | Nitrile |
| Application range | All-round |
| Colour | black |
| Application | reusable |
| Cut protection class | F |
| Type of product | Cut-resistant gloves |