

ELTEN**Welder's boots, black CARL II HI, S3, EU shoe size: 44****Order data**

Order number	092254 44
GTIN	4030839365113
Item class	09P

Description**Version:**

Welder's boot with excellent thermal properties. Heat-resistant up to approx. 200 °C, for short periods up to 300 °C.

- **Upper material of sturdy cowhide.**
- **Leather lining.**
- **Closed tongue.**
- **Basic grey full-size insole.**
- **Anti-static soft fleece fire sole.**
- **Deep-tread rubber/PU SAFETY-GRIP sole.**
- **PU toe protection.**
- **Heat-resistant seams.**
- **Quick release for easy entry.**
- **Padded spark protection sleeve.**

Standard:

EN ISO 20345:2022 S3 SR FO SC LG HI HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 39 – 48.

Technical description

Material of protective toe-cap	Steel
Gender	Gentlemen's
Puncture resistance	Steel
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Protection class	S3
Standard	Inlay type-tested according to DGUV regulation 191
Characteristics	resistant to fuel
Characteristics	ladder grip
Type of product	Safety boots

Accessories

InsolesSensiCare Low EU shoe size 44	092835 44
InsolesSensiCare Medium EU shoe size 44	092836 44
InsolesSensiCare High EU shoe size 44	092837 44