



Thread cutting set with tap sets, 3 pieces, for metric threads: M3-12



Order data

Order number	145119 M3-12
GTIN	4067263118343
Item class	12K

Description

Version:

Strong sheet metal case with carrying handle and 2 offset catches. Each tool is securely stored and protected in a foam insert and is immediately ready to hand. The taps are raised up vertically when the lid is opened. For more detailed descriptions of the content see individual products.

Content:

- 1 each tap set, 3 pieces, No. 130250: Size M3; M4; M5; M6; M8; M10; M12
- 1 each die No. 140330: Size M3; M4; M5; M6; M8; M10; M12
- 1 each jobber drill No. 114031: Size 2.5; 3.3; 4.2; 5; 6.8; 8.5; 10.2
- 1 each adjustable tap wrench No. 148410: Size 1; 2
- 1 toolholder with ratchet No. 148701: Size 85
- 1 each die stock No. 149310: Size 20×5; 20×7; 25×9; 30×11; 38×14
- 1 thread gauge No. 477000: Size M/W
- 1 screwdriver No. 664300: Size 3×60

Technical description

Width	221 mm
Height	55 mm
for metric threads	M3 – 12

Length	416 mm
Thread type	M
Flank angle	60 degrees
Type of product	Die

Accessories

HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 10,2	114030 10,2
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 2,5	114030 2,5
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 3,3	114030 3,3
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 4,2	114030 4,2
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 5	114030 5
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 6	114030 6
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 6,8	114030 6,8
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 8,5	114030 8,5
Hand tap set M M12	130150 M12
Hand tap set M M10	130200 M10
Hand tap set M M12	130200 M12
Hand tap set M M3	130200 M3
Hand tap set M M5	130200 M5
Hand tap set M M6	130200 M6
Hand tap set M M8	130200 M8
Die6g M M10	140330 M10

Die6g M M12	140330 M12
Die6g M M3	140330 M3
Die6g M M4	140330 M4
Die6g M M5	140330 M5
Die6g M M6	140330 M6
Die6g M M8	140330 M8
Sheet metal case empty for thread cutting set for metric threads M3-12	145610 M3-12
Tap wrench, adjustable Type 1	148410 1
Tap wrench, adjustable Type 2	148410 2
T-tap wrench with ratchet Overall length 85 mm	148700 85
Die stock for die Ø × height 20X5 mm	149310 20X5
Die stock for die Ø × height 20X7 mm	149310 20X7
Die stock for die Ø × height 25X9 mm	149310 25X9
Die stock for die Ø × height 30X11 mm	149310 30X11
Die stock for die Ø × height 38X14 mm	149310 38X14
Thread gauge for threads M/W	477000 M/W