

Garant**Fine thread cutting set in a metal case, for metric fine threads: MF3-20****Order data**

Order number	145809 MF3-20
GTIN	4067263118374
Item class	11K

Description**Version:**

Sturdy sheet metal case with carrying handle and 2 catches. Each tool is securely stored and protected in a foam insert and is immediately ready to hand. For more detailed descriptions of the content see individual products.

Content:

1 set each hand tap No. 130470: Size 3×0.35; 4×0.5; 5×0.5; 6×0.75; 8×1; 10×1; 12×1.5; 14×1.5; 16×1.5; 18×1.5; 20×1.5;

1 each die No. 141050: Size 4×0.5; 5×0.5; 6×0.75; 8×1; 10×1; 12×1.5; 14×1.5; 16×1.5; 18×1.5; 20×1.5;

1 each adjustable tap wrench No. 148410: Size 1; 3

1 each die stock No. 149310: Size 20×5; 20×7; 25×9; 30×11; 38×10; 45×14

1 toolholder with ratchet No. 148701: Size 85; 110

1 thread gauge No. 477000: Size M/W

1 screwdriver No. 664300: Size 3×60

Technical description

Thread type	MF
Flank angle	60 degrees

Type of product	Die
-----------------	-----

Accessories

Hand tap set MF 10X1	130470 10X1
Hand tap set MF 12X1,5	130470 12X1,5
Hand tap set MF 14X1,5	130470 14X1,5
Hand tap set MF 16X1,5	130470 16X1,5
Hand tap set MF 18X1,5	130470 18X1,5
Hand tap set MF 20X1,5	130470 20X1,5
Hand tap set MF 3X0,35	130470 3X0,35
Hand tap set MF 4X0,5	130470 4X0,5
Hand tap set MF 5X0,5	130470 5X0,5
Hand tap set MF 6X0,75	130470 6X0,75
Hand tap set MF 8X1	130470 8X1
DieHSS MF 10X1	141050 10X1
DieHSS MF 12X1,5	141050 12X1,5
DieHSS MF 14X1,5	141050 14X1,5
DieHSS MF 16X1,5	141050 16X1,5
DieHSS MF 18X1,5	141050 18X1,5
DieHSS MF 20X1,5	141050 20X1,5
DieHSS MF 4X0,5	141050 4X0,5
DieHSS MF 5X0,5	141050 5X0,5
DieHSS MF 6X0,75	141050 6X0,75
DieHSS MF 8X1	141050 8X1
Sheet metal case empty for fine thread cutting set for metric fine threads MF3-20	145815 MF3-20
Tap wrench, adjustable Type 1	148410 1
Tap wrench, adjustable Type 3	148410 3

Die stock for die \varnothing × height 20X7 mm	149310 20X7
Die stock for die \varnothing × height 25X9 mm	149310 25X9
Die stock for die \varnothing × height 30X11 mm	149310 30X11
Die stock for die \varnothing × height 38X10 mm	149310 38X10
Die stock for die \varnothing × height 45X14 mm	149310 45X14
Thread gauge for threads M/W	477000 M/W