



Welder's boots, black CARL II HI, S3, EU shoe size: 46



Order data

Order number	092254 46
GTIN	4030839365137
Item class	09P

Description

Version:

Welder's boot with excellent thermal properties. Heat-resistant up to approx. 200 °C, for short periods up to 300 °C.

- **Upper material of sturdy cowhide.**
- **Leather lining.**
- **Closed tongue.**
- **Basic grey full-size insole.**
- **Anti-static soft fleece fire sole.**
- **Deep-tread rubber/PU SAFETY-GRIP sole.**
- **PU toe protection.**
- **Heat-resistant seams.**
- **Quick release for easy entry.**
- **Padded spark protection sleeve.**

Standard:

EN ISO 20345:2022 S3 FO SR LG HI HRO

Inlay type-tested according to DGUV regulation 191

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 39 – 48.

Technical description

Data sheet

Material of protective toe-cap	Steel
Characteristics	resistant to fuel
Characteristics	ladder grip
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Gender	Gentlemen's
Protection class	S3
Standard	Inlay type-tested according to DGUV regulation 191
Colour	black
Puncture resistance	Steel
Series	CARL
EU shoe size	46
Type of product	Safety boots

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/092254-46>