

**ELTEN****Shoe, black/blue STEFANO XXSG BOA® black-blue Low ESD S3, EU shoe size: 39**

## Order data

Order number	092270 39
GTIN	4030839362631
Item class	09P

## Description

### Version:

STEFANO safety shoe from the ELTEN WELLMAXX product line.

- **Upper material of sturdy cowhide.**
- **Breathable textile lining.**
- **Closed, padded tongue.**
- **BOA® Fit closure system.**
- **Sole core of Infinergy® from BASF for shock absorption over the entire sole.**
- **Rough SAFETY-GRIP PU/PU sole.**
- **ARTISAN ESD insole.**
- **PU overcap to protect the uppers.**
- **Reflective strips for better visibility.**
- **ESD security.**

### Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

## Technical description

Standard	Inlay type-tested according to DGUV regulation 191
----------	--

Puncture resistance	Textile
Gender	Gentlemen's
Characteristics	Rotary closure
EU shoe size	39
Protection class	S3
Material of protective toe-cap	Steel
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Infinergy sole
Type of product	Safety boots