



Boot, black/blue STEFANO XXSG BOA® black-blue Mid ESD, S3, EU shoe size: 48



Order data

Order number	092271 48
GTIN	4030839362853
Item class	09P

Description

Version:

STEFANO safety shoe from the ELTEN WELLMAXX product line.

- **Upper material of sturdy cowhide.**
- **Breathable textile lining.**
- **Closed, padded tongue.**
- **BOA® Fit closure system.**
- **Sole core of Infinergy® from BASF for shock absorption over the entire sole.**
- **Rough SAFETY-GRIP PU/PU sole.**
- **ARTISAN ESD insole.**
- **PU overcap to protect the uppers.**
- **Reflective strips for better visibility.**
- **ESD security.**

Standard:

EN ISO 20345:2011 S3 SRC

Inlay provision design type tested to DGUV regulations 191.

Technical description

Data sheet

Protection class	S3
Series	STEFANO
Colour	black/blue
EU shoe size	48
Puncture resistance	Textile
Gender	Gentlemen's
Characteristics	Rotary closure
Standard	Inlay type-tested according to DGUV regulation 191
Material of protective toe-cap	Steel
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Infinergy sole
Type of product	Safety boots

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/092271-48>