

Garant
Screw-on toolholder, right-hand, Shank / insert size: 25/12mm

Order data

Order number	260706 25/12
GTIN	4045197653314
Item class	21T

Technical description

Functional width L ₄	32 mm
Head length L ₁	25 mm
Shim screw	269013 5
ISO code toolholder	SSSCR/L 2525M12
Shank size	25 mm
Insert size	12 mm
Pack of insert screws	269028 20
suitable indexable insert	SC.. 1204..
Shim	269005 9
Overall length L	150 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw Type 5	269013 5
Set of insert screws Type 20	269028 20
Shim Type 9	269005 9
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500