

HOLEX®
DCMT 11T308 Set 10 pieces, Grade: HBX130

Order data

| | |
|--------------|---------------|
| Order number | 260506 HBX130 |
| GTIN | 4045197670106 |
| Item class | 22D |

Description

DCMT 11T308 Set of 10 pieces HBX130 Grade: HBX130

Chip breaker: MM

Cutting depth a_p : 0.1 - 3.75 mm

Feed f : 0.06 - 0.36 mm/rev.

Cutting speed v_c main application: 60 - 200 m/min

Technical description

| | |
|--------------------------------------|----------------------|
| Cutting speed v_c main application | 60 - 200 m/min |
| Chip breaker | MM |
| Cutting conditions | slightly interrupted |
| Feed f | 0.06 - 0.36 mm/rev. |
| Cutting depth a_p | 0.1 - 3.75 mm |
| Corner radius | 0.8 mm |
| Main application | M |

| | |
|-------------------------------|------------------------------|
| Grade | HBX130 |
| Finishing/roughing assignment | Finishing |
| Tool material | Carbide |
| ISO code indexable insert | DCMT 11T308 |
| Number of changes/inserts | 2 |
| Type of product | Indexable insert for turning |