

Garant**Screw-on toolholder, right-hand, Shank / insert size: 20/10mm****Order data**

Order number	260606 20/10
GTIN	4045197655363
Item class	21T

Technical description

suitable indexable insert	RC.T 1003
Shim	269005 11
Head length L ₁	17 mm
Shim screw	269013 2
Functional width L ₄	25 mm
ISO code toolholder	SRGCR/L 2020K10
Shank size	20 mm
Insert size	10 mm
Pack of insert screws	269028 2
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Shim Type 11	269005 11
Set of insert screws Type 2	269028 2
Shim screw Type 2	269013 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500