

**Garant****Screw-on toolholder, neutral, Shank / insert size: 25/12mm****Order data**

Order number	260611 25/12
GTIN	4045197653277
Item class	21T

**Technical description**

Shank size	25 mm
Overall length L neutral holders	150 mm
suitable indexable insert	RC.T 1204
Shim screw	269013 2
Pack of insert screws	269028 2
Shim	269005 10
Insert size	12 mm
Overhang L <sub>1</sub> neutral holders	20.3 mm
ISO code toolholder	SRDCN 2525M12
Functional width L <sub>4</sub> neutral holders	18.5 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle $\kappa$	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

---

### Accessories

Set of insert screws Type 2	269028 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 10	269005 10
Shim screw Type 2	269013 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500