



## Workshop vernier caliper in lightweight design, Measuring range: 300mm



### Order data

Order number	412770 300
GTIN	4067263118947
Item class	42A

### Description

#### Version:

Workshop vernier caliper in **lightweight design**. **Parallax-free readings** with the highest contrast due to white scaling on black surface. Optimum guidance and sliding characteristics due to internal double Vee guides. Exchangeable measuring jaws made of hardened stainless steel, precision ground.

#### Optional extras:

Measuring jaws of 125 mm, 150 mm.

### Technical description

Internal jaw $\varnothing$	10 mm
Standard	Works standard
Vernier	1/20
Error limit	0.05 mm
Calibration	A1
Jaw length	90 mm
Packaging	sturdy box
Measuring range	0 - 300 mm
Weight	0.5 kg
Measurement technology	analogue

all parts	hardened
Type of product	Workshop calipers

### Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

### Accessories

Wooden case for vernier caliper size 300 mm	415330 300
---	------------