



Workshop vernier caliper in lightweight design, Measuring range: 500mm



Order data

Order number	412770 500
GTIN	4067263118954
Item class	42A

Description

Version:

Workshop vernier caliper in **lightweight design**. **Parallax-free readings** with the highest contrast due to white scaling on black surface. Optimum guidance and sliding characteristics due to internal double Vee guides. Exchangeable measuring jaws made of hardened stainless steel, precision ground.

Optional extras:

Measuring jaws of 125 mm, 150 mm.

Technical description

Jaw length	90 mm
Calibration	A1
Internal jaw \varnothing	10 mm
Error limit	0.07 mm
Weight	0.6 kg
Packaging	sturdy box
Measuring range	0 - 500 mm
Standard	Works standard
Vernier	1/20
Measurement technology	analogue

all parts	hardened
Type of product	Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500
DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500

Accessories

Wooden case for vernier caliper size 500 mm	415330 500
---	------------