



## Workshop vernier caliper in lightweight design, Measuring range: 200mm



### Order data

Order number	412770 200
GTIN	4067263118930
Item class	42A

### Description

#### Version:

Workshop vernier caliper in **lightweight design**. **Parallax-free readings** with the highest contrast due to white scaling on black surface. Optimum guidance and sliding characteristics due to internal double Vee guides. Exchangeable measuring jaws made of hardened stainless steel, precision ground.

#### Optional extras:

Measuring jaws of 125 mm, 150 mm.

### Technical description

Weight	0.4 kg
Standard	Works standard
Internal jaw $\varnothing$	10 mm
Jaw length	90 mm
Vernier	1/20
Error limit	0.05 mm
Calibration	A1
Packaging	sturdy box
Measuring range	0 - 200 mm
Measurement technology	analogue

all parts	hardened
Type of product	Workshop calipers

### Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

### Accessories

Wooden case for vernier caliper size 200 mm	415330 200
---	------------