

**Garant**
**Screw-on toolholder, left-hand, Shank / insert size: 25/12mm**

**Order data**

Order number	260707 25/12
GTIN	4045197653352
Item class	21T

**Technical description**

Shim	269005 9
suitable indexable insert	SC.. 1204..
Functional width L <sub>4</sub>	32 mm
Insert size	12 mm
ISO code toolholder	SSSCR/L 2525M12
Shank size	25 mm
Pack of insert screws	269028 20
Head length L <sub>1</sub>	25 mm
Shim screw	269013 5
Overall length L	150 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim screw Type 5	269013 5
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 9	269005 9
Set of insert screws Type 20	269028 20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500