

Garant GRIDLINE

Tool cabinet for drawers, can be lifted by crane, 36×24G, Type / number of drawers: 5/0**Order data**

Order number	932400 5/0
GTIN	4067263118183
Item class	9GK

Description**Version:**

Tool cabinet casing in 40×28G, suitable for drawers 36×24G, can be lifted by crane. With 4 rotating eyelets for attaching to load hooks. With two locking rods for secure transport, can be locked with padlock (not included, padlock with a shackle diameter of max. 6 mm is suitable). With 4 U-profile feet for transport by pallet truck, truck forks can be inserted underneath from the front and side. Extremely robust and reinforced frame design made of sheet metal. Suitable drawers can be found under No. 931356.

Colour:

Body RAL 7035 light grey, cover top RAL 7016 anthracite, **powder-coated**.

Note:

Only partially suitable for outdoor use, should not be exposed to weather-related influences.

Technical description

Width	1020 mm
Depth	793 mm
Height	1250 mm

Depth in G	28
Width in G	40
Usable height	900 mm
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------