

Garant GRIDLINE

**Tool cabinet complete with drawers, can be lifted by crane 200 kg, 36×24G,
Type / number of drawers: 5/6****Order data**

Order number	932411 5/6
GTIN	4067263118190
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Cabinet can be centrally locked by a cylinder lock. With 4 rotating eyelets for attaching to load hooks. With two locking rods for secure transport, can be locked with padlock (not included, padlock with a shackle diameter of max. 6 mm is suitable). With 4 U-profile feet for transport by pallet truck, truck forks can be inserted underneath from the front and side. Extremely robust and reinforced frame design made of sheet metal. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Body and drawer body RAL 7035 light grey, drawer fronts and cover top RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey. Cover top not configurable, always RAL 7016 anthracite.**

Attention:

Only partially suitable for outdoor use, should not be exposed to weather-related influences.

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing; the locking rods must have been locked.

Technical description

Drawer usable depth	600 mm
Usable height	900 mm
Drawer usable depth in G	24
Height	1250 mm
Drawer usable area in G	36×24
Drawer usable width	900 mm
Number of drawers	6
Width	1020 mm
Drawer usable width in G	36
Depth	793 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×24G
Type of product	Tool cabinet

Accessories

Lock plate for GridLine Type HU21	914227 HU21
Drawer with one-handed individual drawer release system, 200 kg Drawer front height 100 mm	931356 100
Drawer with one-handed individual drawer release system, 200 kg Drawer front height 125 mm	931356 125

Drawer with one-handed individual drawer release system,200 kg Drawer front height 200 mm	931356 200
Drawer with one-handed individual drawer release system,200 kg Drawer front height 300 mm	931356 300
Drawer with one-handed individual drawer release system,200 kg Drawer front height 75 mm	931356 75
Tool cabinet for drawers, can be lifted by crane Type / number of drawers 5/0	932400 5/0