



Angle grinder Cordless, Type: 71221661



Order data

Order number	077149 71221661
GTIN	4068708005075
Item class	03F

Description

Version:

Fein 18V cordless angle grinder with AMPShare battery technology, for effective cutting, grinding and deburring work in assembly applications.

- **The new FEIN Power Drive motor, which is decoupled from the housing, ensures smooth running and low-vibration operation.**

Powerful and robust angle grinder with low-maintenance Fein Power Drive motor.

- **Electronic speed pre-selection.**

Supplied with:

Without batteries and without charger. Supplied with protective hood, tool-less quick-clamping nut, anti-vibration handle, wrench, L-BOXX.

Note:

Suitable batteries can be found under No. 073856 – 073858 or starter set under No. 073863 – 073867

Technical description

Weight	2 kg
Restart block	yes
Kick-back stop	no
Type of rechargeable battery	Lithium-ion

Power supply	Mains operated
Overload protection	yes
Packaging	Modular case (L-Boxx)
electronic speed pre-selection	yes
Soft start	yes
maximum disc Ø	125 mm
Dead man's circuit	no
maximum vibration to EN	5 m/s ²
Battery voltage	18 V
maximum cutting depth	25 mm
Number of rechargeable batteries contained	0
Manufacturer's designation	CCG18-125-12S AS
maximum speed	2500 - 8500 min ⁻¹
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of product	Angle grinder

Accessories

Li-ion batteryProCore Battery type, battery voltage C18 V	073856 C18
Battery starter setProCore Battery type, battery voltage C18 V	073867 C18