

**Compact angle grinder, Type: 72250660****Order data**

Order number	077111 72250660
GTIN	4068708005426
Item class	03F

Description**Version:****FEIN – Compact angle grinder Ø 125 mm.**

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Technical description

maximum disc Ø	125 mm
maximum vibration to EN	5.1 m/s ²
Mains frequency	50 Hz
Weight	2.2 kg
maximum cutting depth	35 mm

Data sheet

Cable length	4 m
Manufacturer's designation	CG15-125BL
Restart block	yes
Power consumption	1500 W
Special features	Brushless motor
AC supply voltage	230 V
Soft start	yes
maximum speed	3800 - 9000 min ⁻¹
Power supply	Mains-powered
Dead man's circuit	no
Type of product	Angle grinder