

**Angle grinder Cordless, Type: 71221561****Order data**

Order number	077107 71221561
GTIN	4068708004719
Item class	03F

Description**Version:**

Dust-resistant and powerful 18V AMPShare cordless angle grinder for effective cutting, grinding and deburring work in assembly applications. Double the productivity – up to 50% more cuts than the previous system thanks to the perfect combination of a powerful machine and a powerful ProCORE battery system. Durable and robust thanks to completely closed motor housing. This protects the motor from aggressive ceramic and mineral dusts. Innovative cooling ribs ensure optimum cooling, including temperature monitoring.

· Electronic speed pre-selection.**Supplied with:**

Without battery, without charger. Supplied with protective hood, tool-less quick-clamping nut, anti-vibration handle, wrench, L-BOXX.

Note:

See No. 073863 – 073867 for a suitable starter set.

Technical description

suitable battery - supplier / battery type / voltage	Bosch 18 V
Restart block	yes
Manufacturer's designation	CCG18-115-12 AS

Packaging	Modular case (L-Boxx)
maximum cutting depth	25 mm
Type of rechargeable battery	Lithium-ion
Weight	2 kg
maximum vibration to EN	3.7 m/s ²
maximum disc Ø	115 mm
Power supply	Mains operated
Speed range	2500 - 8500 min ⁻¹
Battery voltage	18 V
Type of product	Angle grinder