



Angle grinder Cordless, Type: 71222061



Order data

| | |
|--------------|-----------------|
| Order number | 077149 71222061 |
| GTIN | 4014586900698 |
| Item class | 03F |

Description

Version:

Fein 18V cordless angle grinder with AMPShare battery technology, for effective cutting, grinding and deburring work in assembly applications.

- **The new FEIN Power Drive motor, which is decoupled from the housing, ensures smooth running and low-vibration operation.**

Fein Protago safety angle grinder with a unique operating concept.

- **Safe guidance and two-hand operation by means of an additional handle with contact switch that can be adjusted in 6 positions and cannot be dismantled.**
- **Completely enclosed motor housing protects the motor from aggressive dust.**

Supplied with:

Without batteries and without charger. Supplied with protective hood, tool-less quick-clamping nut, anti-vibration handle, wrench, L-BOXX.

Note:

Suitable batteries can be found under No. 073856 – 073858 or starter set under No. 073863 – 073867

Technical description

| | |
|--|----------------|
| Power supply | Mains operated |
| suitable battery - supplier / battery type / voltage | Bosch 18 V |

| | |
|--|-------------------------------|
| Manufacturer's designation | CCG18-125-12PD-SEC AS |
| Restart block | yes |
| Type of rechargeable battery | Lithium-ion |
| Overload protection | yes |
| maximum speed | 2500 - 8500 min ⁻¹ |
| Number of rechargeable batteries contained | 0 |
| Packaging | Modular case (L-Boxx) |
| Soft start | yes |
| Motor design | brushless |
| Kick-back stop | yes |
| maximum vibration to EN | 4.9 m/s ² |
| maximum disc Ø | 125 mm |
| maximum cutting depth | 25 mm |
| Weight | 2.3 kg |
| Battery voltage | 18 V |
| Dead man's circuit | yes |
| Type of product | Angle grinder |

Accessories

| | |
|--|------------|
| Battery starter setProCore Battery type, battery voltage C18 V | 073867 C18 |
| Li-ion batteryProCore Battery type, battery voltage C18 V | 073856 C18 |