

**Compact angle grinder, Type: 7222906023****Order data**

Order number	077111 7222906023
GTIN	4014586900346
Item class	03F

**Description****Version:****FEIN – Compact angle grinder Ø 125 mm.**

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

**Supplied with:**

Handle, safety guard, clamping nut, wrench.

**Technical description**

Cable length	4 m
maximum cutting depth	35 mm
maximum vibration to EN	6 m/s <sup>2</sup>
Dead man's circuit	no
maximum speed	11500 min <sup>-1</sup>

## Data sheet

Power supply	Mains-powered
Weight	2.4 kg
Mains frequency	50 Hz
Manufacturer's designation	CG17-125
Special features	short body
Soft start	yes
maximum disc Ø	125 mm
Restart block	yes
AC supply voltage	230 V
Power consumption	1700 W
Type of product	Angle grinder