

**Compact angle grinder, Type: 7222916023****Order data**

Order number	077111 7222916023
GTIN	4014586900353
Item class	03F

Description**Version:****FEIN – Compact angle grinder Ø 125 mm.**

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Technical description

Dead man's circuit	no
Cable length	4 m
Power consumption	1700 W
Special features	Electronic speed control
Manufacturer's designation	CG17-125INOX

Data sheet

maximum disc Ø	125 mm
Soft start	yes
Power supply	Mains-powered
Weight	2.4 kg
AC supply voltage	230 V
Restart block	yes
Mains frequency	50 Hz
maximum speed	2200 - 7500 min ⁻¹
maximum vibration to EN	5 m/s ²
maximum cutting depth	35 mm
Type of product	Angle grinder