

AEG

Angle grinder, Type: 4935431730



Order data

Order number	077155 4935431730
GTIN	4002395194902
Item class	07A

Description

Version:

2200 W / 230 mm angle grinder with soft start and restart inhibit.

Supplied with:

Supplied with protective hood, additional handle.

Technical description

Power supply	Mains-powered
maximum speed	6600 min ⁻¹
Power consumption	2200 W
Mains frequency	50 Hz
maximum disc Ø	230 mm
Manufacturer's designation	WS 22-230
maximum vibration to EN	8.7 m/s ²
AC supply voltage	230 V

Soft start	yes
maximum cutting depth	68 mm
Special features	Soft start
Special features	Restart inhibit
Special features	Dead man's switch
Dead man's circuit	yes
Weight	5.2 kg
Restart block	yes
Type of product	Angle grinder