

**Compact angle grinder, Type: 7222896023****Order data**

Order number	077111 7222896023
GTIN	4014586900339
Item class	03F

Description**Version:****FEIN – Compact angle grinder Ø 125 mm.**

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Technical description

maximum vibration to EN	6 m/s ²
maximum disc Ø	125 mm
Restart block	yes
Dead man's circuit	no
Power consumption	1400 W

Manufacturer's designation	CG14-125V
AC supply voltage	230 V
Mains frequency	50 Hz
Power supply	Mains-powered
Special features	Electronic speed control
Cable length	4 m
maximum speed	2800 - 11500 min ⁻¹
maximum cutting depth	35 mm
Weight	2.3 kg
Type of product	Angle grinder