

**Garant****Screw-on toolholder, right-hand, Shank / insert size: 12/09mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 260706 12/09  |
| GTIN         | 4045197655417 |
| Item class   | 21T           |

**Technical description**

|                                 |                               |
|---------------------------------|-------------------------------|
| Shank size                      | 12 mm                         |
| suitable indexable insert       | SC.. 09T3..                   |
| Functional width L <sub>4</sub> | 16 mm                         |
| Insert size                     | 9 mm                          |
| Head length L <sub>1</sub>      | 18 mm                         |
| ISO code toolholder             | SSSCR/L 1212F09               |
| Pack of insert screws           | 269028 2                      |
| Overall length L                | 80 mm                         |
| Standard                        | DIN ISO 5610                  |
| Application type                | right-hand                    |
| Through-coolant                 | no                            |
| Setting angle κ                 | 45 degrees                    |
| Application                     | External longitudinal turning |
| Application                     | External longitudinal turning |
| Type of product                 | Boring bar                    |

---

## Accessories

|  |             |
|--|-------------|
| Set of insert screws Type 2  | 269028 2    |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15                            | 674248 TX15 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500  |