



KOMET KUB Quatron® indexable drill Combination shank, 2×D, Ø DC m7: 14mm



Order data

Order number	235500 14
GTIN	4047109090651
Item class	24P

Description

Version:

With combination shank.

- Optimised coolant channels for reliable chip evacuation.
- Point angle 174° for almost flat-bottomed holes.

Application:

- For stationary and rotating use.
- For difficult drilling conditions (rolling scale, sloping surfaces of castings, interrupted cutting).
- For bores with tolerance ± 0.2 mm.

With indexable inserts No. 236520 – 236576.

Supplied with:

Clamp screws (without indexable inserts).

Note:

Further sizes available on request.

Overhang L_A : 52 mm

Shank $\varnothing D_s$: 20 mm

Shank length L_s : 50 mm

ISO code indexable insert: SOEX 050204 13-..

Pack of insert screws: 239652 6IP1 (0.6 Nm)

Technical description

ISO code indexable insert	SOEX 050204 13-..
Number of cutting edges Z	1

Shank $\varnothing D_s$	20 mm
Reach L_1	28 mm
Pack of insert screws	239652 6IP1 (0.6 Nm)
Shank length L_s	50 mm
Series	KUB Quatron®
Nominal $\varnothing D$	14
Overall length L	102 mm
Overhang L_A	52 mm
Drill depth for indexable insert drill up to	2×D
Shank	DIN 6535 HE, DIN 6595
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	oblique spot drilling
Use for drilling	Cross-drilling
Use for drilling	Centre drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Through-coolant	yes
Type of product	Indexable drill

Accessories

Torque screwdriver, fixed setting set torque 0,6 N·m	211750 0,6
PrecisionBit for Torx Plus®, shank E 6.3 Torx Plus® profile 6IP	674252 6IP
Torx Plus® insert screw set 10 pieces Drive 6IP1	239652 6IP1