

 KOMET

KOMET KUB Quatron® indexable drill Combination shank, 2×D, Ø DC m7: 25mm

Order data

Order number	235500 25
GTIN	4047109047266
Item class	24P

Description
Version:
With combination shank.

- Optimised coolant channels for reliable chip evacuation.
- Point angle 174° for almost flat-bottomed holes.

Application:

- For stationary and rotating use.
- For difficult drilling conditions (rolling scale, sloping surfaces of castings, interrupted cutting).
- For bores with tolerance ± 0.2 mm.

With indexable inserts No. 236520 – 236576.

Supplied with:

Clamp screws (without indexable inserts).

Note:

Further sizes available on request.

Overhang L_A : 74 mm

Shank $\varnothing D_s$: 32 mm

Shank length L_s : 60 mm

ISO code indexable insert: SOEX 07T308 23-..

Pack of insert screws: 239652 8IP1 (1.3 Nm)

Technical description

ISO code indexable insert	SOEX 07T308 23-..
Pack of insert screws	239652 8IP1 (1.3 Nm)

Reach L_1	50 mm
Shank $\varnothing D_s$	32 mm
Number of cutting edges Z	1
Shank length L_s	60 mm
Series	KUB Quatron®
Nominal $\varnothing D$	25
Overall length L	134 mm
Overhang L_A	74 mm
Drill depth for indexable insert drill up to	2×D
Shank	DIN 6535 HE, DIN 6595
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	oblique spot drilling
Use for drilling	Cross-drilling
Use for drilling	Centre drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Through-coolant	yes
Type of product	Indexable drill

Accessories

PrecisionBit for Torx Plus®, shank E 6.3 Torx Plus® profile 8IP	674252 8IP
Torx Plus® insert screw set 10 pieces Drive 8IP1	239652 8IP1
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3