

Garant GREENPLUS

Textile tool rucksack, Type: 1**Order data**

Order number	692210 1
GTIN	4067263125624
Item class	61G

Description**Version:**

The new **GARANT GreenPlus textile bags** combine the best of 2 worlds: They impress with their sustainability while being very comfortable to wear and offering outstanding ergonomics, excellent durability, ideal access and optimum flexibility. They are produced according to the comprehensive and strict standards of the **bluesign®** system, taking into account the needs of people, the environment and resources. Help shape a more sustainable future. With optimised padding system for even better ergonomics and comfort.

Textile tool backpack with 2 main compartments:

- **One main compartment with 2 inside pockets, a robust tool board with 32 shaft pockets and a lockable zip fastener.**
- **One main compartment with 2 separate, padded compartments for laptops up to 15 inches and tablets and a lockable zip fastener.**

Front pocket on the backpack with mobile phone pocket and business card pocket, pen loops, key holder and 2 storage compartments. Small front pocket with orange zip fastener. With compression straps at the side to reduce the volume so that the weight can be carried as close to the body as possible and to allow additional equipment to be attached to the outside.

Anatomically shaped shoulder strap and padded carrying handle. With ergonomic body-contact back system and breast strap for perfect load distribution and optimally balanced, secure seating. Splash-proof base with water edge and 4 stand feet. With elastic outer pockets and a reflective strip for good visibility.

Material:

A combination of 420 denier nylon yarn and 200 denier polyester yarn, for impressive tear-resistant and lightweight performance.

Technical description

Weight	2.3 kg
External dimension height	470 mm
External dimension width	220 mm
External dimension length	350 mm
Sustainability	GARANT GreenPlus
Type of tool storage	Shaft pockets
Type of product	Tool transport system