

Garant**Pipe cutter universal, for Ø to: 54mm****Order data**

Order number	818130 54
GTIN	4067263125129
Item class	81C

Description**Version:**

Extremely sturdy design for very heavy duties. Clean and reliable cut thanks to 4 guide rollers in a row.

Die-cast aluminium body. Quick adjustment spindle with ratchet and spring retraction. With spare cutter wheel No. 818110.

Advantage:

Long working lives due to **TiN coated** cutter wheel. Saves effort and time due to:

- **Ergonomic handle**
- **Lightweight design**
- **needle bearings on the guide rollers and cutter wheel**
- **Detachable manual deburrer with TiN-coated S20 blade.**

Application:

Multi-functional use for cutting stainless steel, aluminium, brass, and copper pipes.

Spare part:

Spare cutter wheel No. 818110.

Technical description

for pipe outer Ø	6 - 54 mm
Weight	720 g
Cutter wheel Ø	19 mm
Cutter wheel bore	4.85 mm
Length	220 - 280 mm

Data sheet

Cutter wheel width	6.2 mm
Height	40 mm
Width	85 mm
Number of guide rollers	4
Number of cutter wheels	1
suitable for pipe material	VA
suitable for pipe material	Aluminium
suitable for pipe material	Brass
suitable for pipe material	Copper
with ratchet function	no
Type of product	Pipe cutters

Accessories

Spare cutter wheel	818110
Wheel pin	819630
Guide roll set with needle bearings 16 pieces	818035