

Garant**Tool set 150 pieces, Type: 692230****Order data**

Order number	685000 692230
GTIN	4067263125662
Item class	61H

Description**Version:**

High-quality **GreenPlus** tool textile bag equipped with handy professional tool as a companion for your day-to-day tasks.

Supplied with:

Hexagonal key L-wrench set, long with spherical head, 9 pieces: 1 pc. No. 627132 size 9

Pliers set, 4 pieces: 1 pc. No. 700001 size 4

Pliers wrench: 1 pc. No. 813501 size 180

Vernier calliper: 1 pc. No. 410100 size 150

Locking tape measure 3 m: 1 pc. No. 461900 size 3

Plastic folding rule 2 m: 1 pc. No. 466200 size 2

Cutter knives: 1 pc. No. 845020

Multi-purpose scissors with 2-component handle, straight: 1 pc. No. 763030 size 205

Bit holder screwdriver: 1 pc. No. 676602 size 30

Bit holder ratchet: 1 pc. No. 676690 size 1/4

Bit set, 61 pieces: 1 pc. No. 676040

Screwdriver set slot-head and Phillips: 1 pc. No. 666956 size 4/2

Socket set 1/4 inch, 41 pieces: 1 pc. No. 630325 size SD

Textile tool roll for open-ended spanners: 1 pc. No. 614835 size 10

Double open-ended spanner: 1 pc. each of No. 610600 size 8×9; 10×11; 12×13; 14×15; 17×19; 18×19; 20×22; 22×24

Universal deburrers: 1 pc. No. 839901 size S10

Hand deburrer: 1 pc. No. 150400 size 12.4

Engineer's hammer: 1 pc. No. 750110 size 300

Carbide multi-purpose drill set, 7 pieces: 1 pc. No. 787078 size 7

Headlamp (HOLEX): 1 pc. No. 081493 size 300

Safety glasses: 1 pc. No. 096200 size CLEAR

Presented in: 1 pc. No. 692230 size 1

Note:

Tool is supplied loose.

Technical description

Number of pieces	150
Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Drive profile	Hexagon screwdriver
Drive profile	Hexagon socket
Drive profile	Screwdriver for TORX® screws
Drive profile	TriWing screwdriver
Drive profile	Screwdriver for TORX® screws with hole
Type of product	Tool set

Accessories

LED headlamp with rechargeable battery Type 300	081493 300
Comfort safety glasses Lens tinting CLEAR	096200 CLEAR
Hand deburrer90° External Ø 12,4 mm	150400 12,4
Vernier caliper Measuring range 150 mm	410100 150
Tape measure Length 3 m	461900 3

Plastic folding rule Length 2 m	466200 2
Double open ended spanner Jaw widths 10X11 mm	610600 10X11
Double open ended spanner Jaw widths 12X13 mm	610600 12X13
Double open ended spanner Jaw widths 14X15 mm	610600 14X15
Double open ended spanner Jaw widths 17X19 mm	610600 17X19
Double open ended spanner Jaw widths 18X19 mm	610600 18X19
Double open ended spanner Jaw widths 20X22 mm	610600 20X22
Double open ended spanner Jaw widths 22X24 mm	610600 22X24
Double open ended spanner Jaw widths 8X9 mm	610600 8X9
Hexagon key L-wrench set, with retainer ballchrome-plated Number of screwdrivers 9	627132 9
Socket set 1/4 inch square drive41 pieces Type SD	630325 SD
Workshop screwdriver set, 6 piecesfor slot-head and Phillips Number of screwdrivers 4/2	666956 4/2
Bit set61 pieces	676040
Screwdriver holder for 1/4 inch bitswith magnet Blade length 30 mm	676602 30
Ratchet bit holder for 1/4 inch bits C 6.3 and E 6.3 Type 1/4	676690 1/4
Textile tool shoulder bag Type 1	692230 1
Pliers set, with grips4 pieces Number of pliers 4	700001 4
Engineer's hammer withhandle protection collar Weight without handle 300 g	750110 300
Multi-purpose shears with 2-component handlesstraight, with adjustable handle opening overall length 205 mm	763030 205
Carbide-tipped multi-purpose drill set Number of drills 7	787078 7
Pliers wrench overall length 180 mm	813501 180
Deburrer / scraper Type S10	839901 S10
General-purpose knife with 2-component handlewith 3 blades, 18 mm	845020