

Groove width gauge, Type: G



Order data

| | |
|--------------|---------------|
| Order number | 484409 G |
| GTIN | 2050002077683 |
| Item class | 48B |

Description

Version:

Groove width gauges with "Go" and "No Go" end. "Go" end with **wear allowance** to DIN 7164. Gauge body of hardened steel.

Groove width gauge with intermediate size and ISO fit, e.g. No. 484409 size **15.8 M6** or numerical tolerance, e.g. 484409 size **41.04 +0.01/-0.02**.

Application:

For checking flat fits, e. g. grooves.

Standard:

Toleranzen und Abmaße nach **DIN EN ISO 1938-1 und DIN 7164**.

Note:

Define the desired tolerance class. When placing the order, specify the **tolerance band (A-ZC)** and basic tolerance quality (7–13) or numerical tolerance. Gauges for precision fit quality 6 and finer tolerances available on request.

Technical description

| | |
|---------|----|
| Quality | 7 |
| Quality | 8 |
| Quality | 9 |
| Quality | 10 |
| Quality | 11 |
| Quality | 12 |

| | |
|-----------------|-------------------|
| Quality | 13 |
| Standard | DIN EN ISO 1938-1 |
| Standard | DIN 7164 |
| Nominal size | 26 - 30 mm |
| Calibration | L6 |
| Type of product | Shaft slot gauge |